

Moisture Analyzers

Lindsey Jahn, Associate Editor



Professional moisture analyzers feature USB, Ethernet and WLAN connectivity for easy data transfer, and can now send measurement reports in A4 or letter format direct to a networked page printer. IN addition to outstanding connectivity, the built-in instrument tests are easy to perform and ensure accurate results. With a five-click guided procedure, the performance of all the instruments together can be qualified thanks to the certified reference substance SmartCal™. Measurement results can be sent directly to a regular A4/letter printer anywhere on the company network. Data also may be transferred to a filer server as a PDF for on-screen viewing and electronic archiving, as well as standard CSV or XLS format for interchange with laboratory and office software.

Mettler-Toledo, www.mt.com [1]

Source URL (retrieved on 01/28/2015 - 6:21pm):

<http://www.foodmanufacturing.com/product-releases/2014/02/moisture-analyzers>

Links:

[1] <http://www.mt.com>